

TIMING BELT SELECTION CHART	2
NEOPRENE TIMING BELTS	
MXL – .080" Pitch.....	3
XL – 1/5" Pitch.....	6
L – 3/8" Pitch.....	8
HTD® – 3 mm Pitch.....	10
HTD® – 5 mm Pitch.....	12
GT®2 – 2 mm Pitch.....	14
GT®2 – 3 mm Pitch, Single- & Double-Sided.....	16
GT®2 – 5 mm Pitch, Single- & Double-Sided.....	20
TruMotion® TIMING BELTS	
Specifications.....	23
MXL – .080" Pitch.....	24
XL – 1/5" Pitch.....	26
L – 3/8" Pitch.....	28
GT®2 – 2 mm Pitch.....	29
GT®2 – 3 mm Pitch.....	30
GT®2 – 5 mm Pitch.....	31
TIMING BELT CLAMPS	
MXL, XL, GT®2 – 2 mm Pitch, HTD® & GT®2 – 3 & 5 mm Pitches, Polycarbonate.....	32
XL & L – 1/5" & 3/8" Pitches Aluminum.....	33
HTD® – 5 & 8 mm Pitches, Aluminum.....	34
GT®2 – 2 & 3 mm Pitches, Aluminum.....	35
GT®2 – 5 & 8 mm Pitches, Aluminum.....	36
AT – 5 & 10 mm Pitches, Aluminum.....	37
T – 5 & 10 mm Pitches, Aluminum.....	38
TIMING BELT PULLEYS	
L – 3/8" Pitch, Steel.....	39
HTD® – 8 mm Pitch, Nylon with Aluminum Insert.....	40
GT®2 – 2 mm Pitch, Polycarbonate.....	42
GT®2 – 3 mm Pitch, Polycarbonate.....	43
CONIDRIVE® SYSTEM	
Application Examples.....	44
Design Data.....	45
Timing Belts & Belt Stock.....	48
Mounting Plates.....	49
Pulleys.....	50
LADDER CHAIN, SPROCKETS AND POSI-DRIVE BELTS	
Ladder Chain & Sprockets – .185" (4.7 mm) Pitch, Acetal with Metal Insert.....	52
Ladder Chain & Sprockets – .353" (8.9 mm) Pitch, Acetal with Metal Insert.....	54
Posi-Drive Belts – 32 Pitch (CP 2.5 mm).....	57