





GT[®]2 Double-Sided Timing Belts – 5 mm Pitch

Stock Drive Products/Sterling Instrument ■ Phone: 516-328-3300 ■ Fax: 516-326-8827


- **TRUE METRIC[®]** PROFILE
- **NEOPRENE**
- **9 & 15 mm WIDE**



NOTE: Dimensions in () are inch size.

MATERIAL: Nylon Covered, Fiberglass Reinforced, Neoprene
BREAKING STRENGTH: 385 N per 1 mm (275 lbs per 1/8) belt width; not representative of the load-carrying capacity of the belt.
WORKING TENSION: 712 N for 25.4 mm belt (160 lbs for 1 in. belt). For more information, see the technical section.
TEMPERATURE RANGE: -34°C to +85°C (-30°F to +185°F)

CATALOG NUMBER DESIGNATION:



Width Code	Belt Width	Equivalent Inch Width
090	9 mm	.354
150	15 mm	.591

Example: A 6R55MD085150 is a 85 Groove 15 mm Wide Belt.

Groove Code	Pitch Length	
	mm	Inch
080	400	15.748
081	405	15.945
085	425	16.732
090	450	17.717
100	500	19.685
107	535	21.063
113	565	22.244
115	575	22.638
116	580	22.835
120	600	23.622
125	625	24.606
130	650	25.591
140	700	27.559
142	710	27.953
148	740	29.134
149	745	29.331
150	750	29.528

Groove Code	Pitch Length	
	mm	Inch
153	765	30.118
158	790	31.102
160	800	31.496
163	815	32.087
166	830	32.677
167	835	32.874
170	850	33.465
174	870	34.252
178	890	35.039
180	900	35.433
185	925	36.417
190	950	37.402
195	975	38.359
197	985	38.779
200	1000	39.370
210	1050	41.339
223	1115	43.898

Groove Code	Pitch Length	
	mm	Inch
225	1125	44.291
230	1150	45.276
239	1195	47.047
250	1250	49.213
254	1270	50.000
259	1295	50.984
260	1300	51.181
275	1375	54.134
284	1420	55.905
290	1450	57.087
315	1575	62.008
319	1595	62.795
320	1600	62.992
327	1635	64.370
338	1690	66.535
344	1720	67.716
351	1755	69.094

Groove Code	Pitch Length	
	mm	Inch
358	1790	70.472
360	1800	70.866
379	1895	74.606
389	1945	76.575
396	1980	77.953
400	2000	78.740
422	2110	83.071
450	2250	88.583
505	2525	99.409
552	2760	108.661
624	3120	122.834
634	3170	124.803
640	3200	125.984
686	3430	135.039
760	3800	149.606

Special Widths - cut to size from sleeves available from stock.
 Pulleys are available with metric or inch standards.