





AC Induction

Product Image	Part Number	Specifications	Voltage DC	Number of Channels	Max. Amperage per Channel	Continuous Amperage	Mode of Operation	Output Communication
	NR4-SIM1360	Download Spec Sheet	12-60	1	30	20	Speed and Position Control	CanOpen RS232
	NR4-FIM2360T	Download Spec Sheet	12-60	2	60	40	Speed and Position Control	CanOpen RS232
	NR4-FIM2360TS	Download Spec Sheet	12-60	1	120	80	Speed and Position Control	CanOpen RS232

AC Induction

Product Image	Part Number	Specifications	Voltage DC	Number of Channels	Max. Amperage per Channel	Continuous Amperage	Mode of Operation	Output Communication
	NR4-FIM2360TE	Download Spec Sheet	12-60	2	60	40	Speed and Position Control	CanOpen RS232 Ethernet