

# PIPE SHAFTS

# SDP/SI

BEARINGS STEEL  
WEIGHT REDUCTION  
DESIGN FLEXIBILITY

PHONE: 516.328.3300 • FAX: 516.326.8827 • WWW.SDP-SI.COM




**> MATERIAL:**

AISI 52100 Steel, Hardened  
to HRC 58...62

**> STRAIGHTNESS:**

0.0003 mm/mm

Other lengths available  
upon request.



### METRIC COMPONENT

Catalog Number	d Bore ± 0.5	D Diameter g6	D Tolerance	L Length	Case Depth				
S40LPSM02060100	2	6	-0.004/-0.012	100	1				
S40LPSM02060150				150					
S40LPSM02060200				200					
S40LPSM02060300				300					
S40LPSM03080100	3	8	-0.005/-0.014	100	1				
S40LPSM03080150				150					
S40LPSM03080200				200					
S40LPSM03080300				300					
S40LPSM03080400	400	4	-0.005/-0.014	100	1				
S40LPSM04100100	150								
S40LPSM04100150	200								
S40LPSM04100200	300								
S40LPSM04100300	400	5	-0.006/-0.017	500	1				
S40LPSM04100400	600								
S40LPSM04100500	200			6		-0.006/-0.017	300	1	
S40LPSM06120200	400								
S40LPSM06120300	500								
S40LPSM06120400	600								
S40LPSM06120500	800	8	-0.006/-0.017	300	1.5				
S40LPSM06120600	400								
S40LPSM06120800	500								
S40LPSM10160300	600			10		-0.006/-0.017	800	1	
S40LPSM10160400	1000								
S40LPSM10160500	300	14	-0.007/-0.020		400		1.5		
S40LPSM10160600	500								
S40LPSM10160800	600								
S40LPSM10161000	800								
S40LPSM14200300	14	20	-0.007/-0.020	1000	1.5				
S40LPSM14200400				300		17	-0.007/-0.020	400	1.5
S40LPSM14200500				500					
S40LPSM14200600				600					
S40LPSM14200800	800								
S40LPSM14201000	1000	25	-0.007/-0.020	300	1.5				
S40LPSM17250300	400								
S40LPSM17250400	500								
S40LPSM17250500	600								
S40LPSM17250600	800	17	-0.007/-0.020	800	1.5				
S40LPSM17250800	1000								
S40LPSM17251000									

3-8  
D805

I

R

T

1

2

3

4

5

6

7

8

9

10

11

12

13

14

15

A