








**GT®2 Timing Belt Clamp Kit – 5 mm & 8 mm Pitch**

Stock Drive Products/Sterling Instrument ■ Phone: 516-328-3300 ■ Fax: 516-326-8827

**■ USED IN LINEAR DRIVES**



5 mm PITCH						
F mm (in.)	M mm (in.)	S mm (in.)	H mm (in.)	K mm (in.)	X mm (in.)	S <sub>1</sub> mm (in.)
7.5 (.295)	10 (.394)	8 (.315)	10 (.394)	25 (.984)	5 (.197)	10 (.394)

8 mm PITCH						
F mm (in.)	M mm (in.)	S mm (in.)	H mm (in.)	K mm (in.)	X mm (in.)	S <sub>1</sub> mm (in.)
10 (.394)	16 (.630)	15 (.591)	15 (.591)	40 (1.575)	8 (.315)	16 (.630)

**MATERIAL:** Aluminum

Timing Belt Clamp Kit Includes:  
Top and Bottom Plate and Hardware for Assembly

Sold as Kit

GT®2 • 5 mm PITCH							Toothed + Flat Plate Total Weight (with hardware) kg (lb.)
Catalog Number	Belt Width mm (in.)	A mm (in.)	B mm (in.)	C mm (in.)	D mm (in.)	E mm (in.)	
A16A55M09	9 (.354)	45 (1.772)	5 (.197)	30.5 (1.201)	5.5 (.217)	15.5 (.610)	0.056 (.12)
A16A55M15	15 (.591)			37 (1.457)		22 (.866)	
A16A55M25	25 (.984)			47 (1.850)		32 (1.260)	

GT®2 • 8 mm PITCH							Toothed + Flat Plate Total Weight (with hardware) kg (lb.)
Catalog Number	Belt Width mm (in.)	A mm (in.)	B mm (in.)	C mm (in.)	D mm (in.)	E mm (in.)	
A16A58M20	20 (.787)	72 (2.835)	8 (.315)	50.5 (1.988)	9 (.354)	30.5 (1.201)	0.272 (.60)
A16A58M30	30 (1.181)			60.5 (2.382)		40.5 (1.594)	
A16A58M50	50 (1.968)			81 (3.189)		61 (2.401)	

**NOTE:** Hardware for kit includes screws, washers and hex nuts for assembly.  
For replacement hardware kit, order: **A16A55MBOLTKIT** GT®2 5 mm Pitch  
**A16A58MBOLTKIT** GT®2 8 mm Pitch