

BELT WIDTHS

METRIC - 6, 9, 15 & 25 mm

TRUE METRIC® PROFILE

➤ MATERIAL:

Nylon Covered, Fiberglass Reinforced, Neoprene

➤ SPECIFICATIONS:

Breaking Strength:

316 N per 1 mm (226 lbf per 1/8 in.) Belt Width; not representative of the load-carrying capacity of the belt.

Working Tension:

454 N for 25.4 mm belt (102 lbf for 1 in. belt).

For more information, see the technical section.



Temperature Range:

-34°C to +85°C (-30°F to +185°F)

➤ MODIFICATIONS:

Special Widths - cut to size from sleeves available from stock.

Pulleys are available with metric or inch standards.



NOTE: Dimensions in () are inch.

METRIC COMPONENT
CATALOG NUMBER

A 6 R 25 M D

No. of
Grooves
Code

Belt Width mm	Width Code
6 (.236)	060
9 (.354)	090
15 (.591)	150
25 (.984)	250

Groove Code	Pitch Length	
	mm	Inch
080	400	15.748
083	415	16.339
085	425	16.732
090	450	17.717
092	460	18.110
095	475	18.701
096	480	18.898
099	495	19.488
100	500	19.685
104	520	20.472
107	535	21.063
111	555	21.850
112	560	22.047
113	565	22.244
115	575	22.638
116	580	22.835
117	585	23.031
118	590	23.228
120	600	23.622
122	610	24.016
123	615	24.213
127	635	25.000
128	640	25.197
131	655	25.787
133	665	26.181
134	670	26.378

Groove Code	Pitch Length	
	mm	Inch
136	680	26.772
137	685	26.968
139	695	27.362
140	700	27.559
142	710	27.953
148	740	29.134
149	745	29.331
151	755	29.724
153	765	30.118
155	775	30.512
158	790	31.102
160	800	31.496
166	830	32.677
167	835	32.874
170	850	33.465
174	870	34.252
178	890	35.039
185	925	36.417
186	930	36.614
187	935	36.811
190	950	37.402
195	975	38.386
197	985	38.779
200	1000	39.370
207	1035	40.748
210	1050	41.339

Continued on the next page

I

R

T

1

2

3

4

5

6

7

8

9

10

11

12

13

14

15

A



0 10

METRIC COMPONENT
CATALOG NUMBERA 6 R 2 5 M D No. of
Grooves
Code

Belt Width mm	Width Code
6 (.236)	060
9 (.354)	090
15 (.591)	150
25 (.984)	250

Groove Code	Pitch Length	
	mm	Inch
220	1100	43.307
225	1125	44.291
239	1195	47.047
240	1200	47.244
245	1225	48.228
250	1250	49.213
254	1270	50.000
259	1295	50.984
275	1375	54.134
284	1420	55.905
300	1500	59.055
315	1575	62.008
319	1595	62.795
327	1635	64.370
338	1690	66.535
358	1790	70.472
360	1800	70.866
374	1870	73.622
379	1895	74.606
389	1945	76.575
396	1980	77.953
400	2000	78.740
420	2100	82.677
422	2110	83.071
450	2250	88.583
470	2350	92.520
505	2525	99.409
552	2760	108.661
624	3120	122.834

Continued from the previous page