





GT®2 Double-Sided Timing Belts – 3 mm Pitch

Stock Drive Products/Sterling Instrument Phone: 516-328-3300 Fax: 516-326-8827

- **TRUE METRIC®** PROFILE
- **NEOPRENE**
- **6 & 9 mm WIDE**



NOTE: Dimensions in () are inch size.

Continued on the next page

- MATERIAL:** Nylon Covered, Fiberglass Reinforced, Neoprene
BREAKING STRENGTH: 190 N per 1 mm (135 lbs per 1/8) belt width;
 not representative of the load-carrying capacity of the belt.
WORKING TENSION: 507 N for 25.4 mm belt (114 lbs for 1 in. belt).
 For more information, see the technical section.
TEMPERATURE RANGE: -34°C to +85°C (-30°F to +185°F)

CATALOG NUMBER DESIGNATION:

A 6 R 5 3 M D

No. of Grooves Code (See tables below) **Width Code** (See right)

Width Code	Belt Width	Equivalent Inch Width
060	6 mm	.236
090	9 mm	.354

Example: A 6R53MD125090 is a 125 Groove 9 mm Wide Belt.

Groove Code	Pitch Length	
	mm	Inch
124	372	14.646
125	375	14.764
127	381	15.000
128	384	15.118
129	387	15.236
130	390	15.354
131	393	15.472
132	396	15.591
133	399	15.709
135	405	15.945
137	411	16.181
138	414	16.299

Groove Code	Pitch Length	
	mm	Inch
139	417	16.417
140	420	16.535
142	426	16.772
144	432	17.008
145	435	17.126
146	438	17.244
148	444	17.480
149	447	17.598
153	459	18.071
155	465	18.307
156	468	18.425
157	471	18.543

Groove Code	Pitch Length	
	mm	Inch
158	474	18.661
160	480	18.898
161	483	19.016
162	486	19.134
163	489	19.252
164	492	19.370
167	501	19.724
168	504	19.842
170	510	20.079
171	513	20.197
173	519	20.433
175	525	20.669

Groove Code	Pitch Length	
	mm	Inch
176	528	20.787
177	531	20.905
179	537	21.142
184	552	21.732
186	558	21.968
188	564	22.205
190	570	22.441
192	576	22.677
195	585	23.031
197	591	23.268
199	597	23.504
200	600	23.622

Special Widths - cut to size from sleeves available from stock.
 Pulleys are available with metric or inch standards.



GT®2 Double-Sided Timing Belts – 3 mm Pitch

Stock Drive Products/Sterling Instrument ■ Phone: 516-328-3300 ■ Fax: 516-326-8827

- **TRUE METRIC®** PROFILE
- **NEOPRENE**
- **6 & 9 mm WIDE**

Continued from the previous page

CATALOG NUMBER DESIGNATION:

A 6 R 5 3 M D

No. of Grooves Code (See tables below) **Width Code** (See right)

Width Code	Belt Width	Equivalent Inch Width
060	6 mm	.236
090	9 mm	.354

Example: A 6R53MD245090 is a 245 Groove 9 mm Wide Belt.

Groove Code	Pitch Length	
	mm	Inch
202	606	23.858
203	609	23.976
204	612	24.094
209	627	24.685
210	630	24.803
211	633	24.921
213	639	25.157
215	645	25.394
216	648	25.512
218	654	25.748
219	657	25.866
221	663	26.102
223	669	26.339
228	684	26.929

Groove Code	Pitch Length	
	mm	Inch
229	687	27.047
232	696	27.402
237	711	27.992
245	735	28.937
246	738	29.055
250	750	29.528
251	753	29.646
262	786	30.945
265	795	31.299
274	822	32.362
279	837	32.953
280	840	33.071
281	843	33.189
291	873	34.370

Groove Code	Pitch Length	
	mm	Inch
294	882	34.724
297	891	35.079
300	900	35.433
305	915	36.024
315	945	37.205
317	951	37.441
327	981	38.622
334	1002	39.449
342	1026	40.394
345	1035	40.748
350	1050	41.339
352	1056	41.575
354	1062	41.811
360	1080	42.520

Groove Code	Pitch Length	
	mm	Inch
375	1125	44.291
385	1155	45.472
397	1191	46.890
421	1263	49.724
445	1335	52.559
500	1500	59.055
504	1512	59.527
512	1536	60.472
529	1587	62.480
652	1956	77.008
668	2004	78.897
687	2061	81.142

Special Widths - cut to size from sleeves available from stock.
Pulleys are available with metric or inch standards.