




XL Timing Belts – 1/5" or 5.08 mm Pitch

Stock Drive Products/Sterling Instrument Phone: 516-328-3300 Fax: 516-326-8827

- PowerGrip® TruMotion®
- 1/4, 5/16 & 3/8 INCH - 6, 8 & 9.5 mm WIDE
- NON-MARKING
- POLYMER COMPOUND
- LOW DUST
- RoHS COMPLIANT



NOTE: Dimensions in () are mm.



Continued on the next page

MATERIAL: Cream-Colored Polymer Compound, Fiberglass Reinforced Body with Nylon Tooth Facing for Reduced Dust

BREAKING STRENGTH: 113 lbs per 1/8 (158 N per 1 mm) belt width; not representative of the load-carrying capacity of the belt.

WORKING TENSION: 23 lbs for 1 in. belt (102 N for 25.4 mm belt).

For more information, see the technical section.

TEMPERATURE RANGE: -40°F to +220°F (-40°C to +104°C)

CATALOG NUMBER DESIGNATION:		Width Code	Belt Width	Example	
I N C H	A 2 6 R 3 – <input type="checkbox"/> <input type="checkbox"/> <input type="checkbox"/> <input type="checkbox"/> <input type="checkbox"/> <input type="checkbox"/>	025 031 037	1/4 5/16 3/8	A26R 3-034037 is a 34 Groove 3/8 Wide Belt.	
	No. of Grooves Code				Width Code
	(See tables below)				(See right)
M E T R I C	A 2 6 R 3 M <input type="checkbox"/> <input type="checkbox"/> <input type="checkbox"/> <input type="checkbox"/> <input type="checkbox"/> <input type="checkbox"/>	060 080 095	6 mm 8 mm 9.5 mm	A26R 3M060080 is a 60 Groove 8 mm Wide Belt.	
	No. of Grooves Code				Width Code
	(See tables below)				(See right)

Groove Code	Pitch Length	
	Inch	mm
021	4.2	106.68
025	5.0	127
027	5.4	137.16
028	5.6	142.24
029	5.8	147.32
030	6.0	152.4
031	6.2	157.48
032	6.4	162.56
033	6.6	167.64
034	6.8	172.72
035	7.0	177.8
036	7.2	182.88

Groove Code	Pitch Length	
	Inch	mm
037	7.4	187.96
038	7.6	193.04
039	7.8	198.12
040	8.0	203.2
041	8.2	208.28
042	8.4	213.36
043	8.6	218.44
044	8.8	223.52
045	9.0	228.6
046	9.2	233.68
047	9.4	238.76
048	9.6	243.84

Groove Code	Pitch Length	
	Inch	mm
049	9.8	248.92
050	10.0	254
051	10.2	259.08
053	10.6	269.24
054	10.8	274.32
055	11.0	279.4
056	11.2	284.48
057	11.4	289.56
058	11.6	294.64
060	12.0	304.8
061	12.2	309.88
062	12.4	314.96

Groove Code	Pitch Length	
	Inch	mm
063	12.6	320.04
064	12.8	325.12
065	13.0	330.2
066	13.2	335.28
067	13.4	340.36
068	13.6	345.44
069	13.8	350.52
070	14.0	355.6
071	14.2	360.68
072	14.4	365.76
073	14.6	370.84
074	14.8	375.92

Special Widths - cut to size from sleeves available from stock.
Pulleys are available with inch or metric standards.

