





Stroke Adjust. Shaft Collars & Rubber Bumpers

Stock Drive Products/Sterling Instrument ■ Phone: 516-328-3300 ■ Fax: 516-326-8827

- EASY AND PRECISE STROKE ADJUSTMENT
- UP TO .44 IN. FINE STROKE ADJUSTMENT




Catalog Number		O.D.	B +.001 -.000	Min. Width	Max.* Travel	Screw 1	Screw 2	Max. Axial Load Capacity lb.	
Stainless Steel	Carbon Steel, Black Oxide							Stainless Steel	Steel
S21SAC-025063	S21SAC-025063S	5/8	.250	15/32	.19	#4-40	#2-56	390	790
S21SAC-038088	S21SAC-038088S	7/8	.375	15/32	.16	#6-32	#2-56	460	660
S21SAC-050113	S21SAC-050113S	1-1/8	.500	3/4	.32	#8-32	#5-40	690	1310
S21SAC-063131	S21SAC-063131S	1-5/16	.625	3/4	.32	#8-32	#6-32	570	1210
S21SAC-075150	S21SAC-075150S	1-1/2	.750	7/8	.38	#10-32	#6-32	1200	3600
S21SAC-100175	S21SAC-100175S	1-3/4	1.000	7/8	.38	#10-32	#8-32	730	3450
S21SAC-125206	S21SAC-125206S	2-1/16	1.250					2450	3260
S21SAC-138225	S21SAC-138225S	2-1/4	1.375	1	.44	1/4-20	#8-32	2640	3220
S21SAC-150238	S21SAC-150238S	2-3/8	1.500					2840	3180

*Max. Width = Min.Width + Max. Travel

- OIL- AND CHEMICAL-RESISTANT

- SHOCK ABSORBER FOR COMPRESSION LOADS



MATERIAL: Buna N70 Durometer
OPERATING TEMPERATURE: -20°F to +250°F

Catalog Number	I.D.	O.D.
S79RUB-025063	.25	.63
S79RUB-038088	.38	.88
S79RUB-050113	.50	1.13
S79RUB-063131	.63	1.31
S79RUB-075150	.75	1.50
S79RUB-100175	1.00	1.75
S79RUB-125206	1.25	2.06
S79RUB-138225	1.38	2.25
S79RUB-150238	1.50	2.38