

Overview: Brushless Motor Controllers

Part Number	Number of Channel	Amps per Channel	Max DC Voltage	IP Rating	Safe Torque Off	Ethernet
NR4 - SBLMG1360T	1	40	60	40	Yes	No
NR4 - SBL1360A	1	30	60	40	No	No
NR4 - SBL2360T	2	30	60	40	Yes	No
NR4 - SBL2360TS	1	60	60	40	Yes	No
NR4 - SBLM2360T *	2	30	60	40	Yes	No
NR4 - SBLM2360TS *	1	60	60	40	Yes	No
NR4 - KBL1660	1	120	60	65	Yes	No
NR4 - MBL1660A	1	120	60	40	No	No
NR4 - FBL2360T	2	60	60	40	Yes	No
NR4 - FBL2360TS	1	120	60	40	Yes	No
NR4 - FBL2360TE	1	60	60	40	Yes	Yes
NR4 - FBL2360TES	2	120	60	40	Yes	Yes
NR4 - GBL2660	2	180	60	51	Yes	No
NR4 - GBL2660S	1	360	60	51	Yes	No
NR4 - GBL2660E	2	180	60	51	Yes	Yes
NR4 - GBL2660ES	1	360	60	51	Yes	Yes
NR4 - RGBL1860	1	400	60	56	No	No

* = The SBLM2360 series differs from the SBL2360 as it comes with Molex connectors and dedicated PWM brake outputs

Overview: Brushed Motor Controllers

Part Number	Number of Channel	Amps per Channel	Max DC Voltage	IP Rating	Safe Torque Off	Ethernet	Resolver
NR4 - SDC2160	2	20	30	40	No	No	No
NR4 - SDC2160S	1	40	60	40	No	No	No
NR4 - SDC3260T	3	20	60	40	Yes	No	No
NR4 - MDC2460	2	60	60	40	No	No	No
NR4 - MDC1460	2	120	60	40	No	No	No
NR4 - FDC3260T	3	60	60	40	Yes	No	Yes
NR4 - FDC3260TE	3	60	60	65	Yes	Yes	Yes
NR4 - GDC3660	3	180	60	51	No	No	No
NR4 - GDC3660E	3	180	60	51	No	Yes	No
NR4 - RGDC1860	1	300	60	56	No	No	No