

Motor frame size (mm)	060LD		060AD	
Voltage (Vdc)	48		24	
Frame length	A	B	A	B
Continuous stall torque (Nm)	0.64	1.28	0.64	1.28
Peak torque (Nm)	1.92	3.84	1.92	3.84
Standard inertia (kgcm ²)	0.18	0.33	0.18	0.33
Winding thermal time constant (sec)	47	51	47	51
Standard motor weight (kg)	1.6	2.0	1.6	2.0
Number of poles	10	10	10	10
Speed 3000 (rpm)	6,000		3,000	
Kt (Nm/A)	0.07		0.07	
Ke (V/krpm)	4.4		4.4	
Rated torque (Nm)	0.64	1.28	0.64	1.28
Stall current (A)	9.2	18.3	9.2	18.3
Rated power (kW)	0.4	0.8	0.2	0.4
R (ph-ph) (Ohms)	0.20	0.07	0.20	0.07
L (ph-ph) (mH)	0.43	0.21	0.43	0.21
Standard Connection	Flying Leads		Flying Leads	